




|    |                |                                                    |   |
|----|----------------|----------------------------------------------------|---|
| 1  | 611/00100      | Hose                                               | 1 |
| 2  | 611/00100      | Hose                                               | 1 |
| 3  | 611/00100      | Hose                                               | 1 |
| 4  | 120/40301      | Housing                                            | 4 |
| 5  | 1604/0002      | Adapter<br>Supersession >                          | 7 |
| 6  | 892/00055      | Plug blanking 1/4"BSP coned<br>Supersession >      | 1 |
| 7  | 1406/0011      | Washer Bonded 1/4"BSP<br>< Supersession            | 8 |
| 8  | 904/09400      | Seal piston hyd clamping<br>< Supersession         | 4 |
| 9  | ⊘ Not for sale | Pin lock<br>> No Longer Available                  | 4 |
| 10 | 823/00016      | Washer 1/8in<br>< Supersession<br>Alternatives     | 4 |
| 10 | 823/00017      | Washer 3/16in                                      | 4 |
| 11 | ⊘ Not for sale | Washer tab<br>Supersession >                       | 4 |
| 12 | 826/00820      | Nut                                                | 4 |
| 13 | 611/41200      | Hose<br>< Supersession                             | 1 |
| 14 | 611/22100      | Hose 1/4"BSP x 500mm<br><M292236<br>< Supersession | 1 |
| 14 | ⊘ Not for sale | Hose                                               | 1 |
| 15 | 631/30100      | Hose 1/4" x 400mm                                  | 1 |
| 16 | 1604/0002      | Adapter<br>Supersession >                          | 2 |
| 17 | 1406/0011      | Washer Bonded 1/4"BSP<br>< Supersession            | 2 |
|    |                |                                                    |   |

|    |                |                                                                         |   |
|----|----------------|-------------------------------------------------------------------------|---|
| 18 | ⊘ Not for sale | Valve check<br>< Supersession                                           | 1 |
| 19 | :2401/0201     | O Ring<br>< Supersession                                                | 2 |
| 20 | :826/00034     | Clip 'E'                                                                | 1 |
| 21 | ⊘ Not for sale | Pin tension                                                             | 2 |
| 22 | ⊘ Not for sale | Lever                                                                   | 1 |
| 23 | ⊘ Not for sale | Screw 1/4 UNF x .625<br>Supersession >                                  | 1 |
| 24 | ⊘ Not for sale | Pin tension                                                             | 1 |
| 25 | :150/14303     | Knob Small dia.                                                         | 1 |
| 26 | ⊘ Not for sale | Spring                                                                  | 1 |
| 27 | ⊘ Not for sale | Ball                                                                    | 1 |
| 28 | :1406/0019     | Washer Bonded                                                           | 1 |
| 29 | 816/60062      | Adapter<br>Supersession >                                               | 1 |
| 30 | :1604/0002     | Adapter<br>Supersession >                                               | 1 |
| 31 | :1604/0002     | Adapter<br>Supersession >                                               | 1 |
| 32 | :1406/0011     | Washer Bonded 1/4"BSP<br>< Supersession                                 | 2 |
| 33 | ⊘ Not for sale | Bolt<br>Supersession >                                                  | 2 |
| 34 | ⊘ Not for sale | Nut<br>Supersession >                                                   | 2 |
| 35 | ⊘ Not for sale | Seal                                                                    | 1 |
| 36 | 816/00464      | Adaptor Elbow 90 1/4 BSP (F), 1/4 BSP (M)<br><M392236<br>Supersession > | 1 |