




262312

1	834/00633	Hose elbow	1
2	⊘ Not for sale	Pipe suction 2ws Supersession >	1
3	648/02902	Hose low pressure, 150mm < Supersession	1
4	2201/0013	Clip wormdrive 59/83mm < Supersession	8
5	⊘ Not for sale	'See Remark' Pump see E2-2-1	1
6	615/20200	Hose <NOV-2001	1
6	629/80036	Hose	1
7	126/01460	Pipe assembly	1
8	:45/908000	Plug Test Point SAE 892/00706 is the mate. Or 892/01234 adaptor w/ hose	1
9	1315/3310Z	Bolt M8 x 40mm	2
10	1420/0007Z	Washer (M8) Supersession >	3
11	1370/0203Z	Nut Lock, M8 < Supersession	2
12	1315/0410Z	Setscrew M10 x 40 < Supersession	2
13	1425/0008Z	Spring Washer M10 Supersession >	2
14	1420/0008Z	Washer Plain M10 Supersession >	2
15	826/01249	Nut Rivet M10	2
16	⊘ Not for sale	Hose	1
19	615/48200	Hose	1
20	⊘ Not for sale	Pipe return centremount > No Longer Available	1
21	635/32200	Hose 3/4"BSP x 460mm	1

22	1606/0009	Adapter Reducing G3/4A G1/2A < Supersession	1
23	637/31900	Hose	1
24	614/20300	Hose 5/8" BSP 500 mm	1
25	635/30800	Hose	1
26	⊘ Not for sale	Pipe 2ws oil cooler Supersession >	1
27	649/43700	Hose	1
28	648/02536	Hose low pressure Supersession > 640mm long	1
29	2201/0005	Clip Worm Drive 14/27mm < Supersession	6
30	⊘ Not for sale	'See Remark' See E1-18-1	1
31	123/07424	Valve dual check Supersession >	1
32	G8/9	Plug	1
33	1406/0008	Washer Bonded 10mm < Supersession	1
34	821/00188	Insert Clamp Supersession > Use with item 19 & 20	2
35	821/00186	Clamp Top 25mm Supersession > Use with item 19 & 20	2
36	821/00187	Clamp Base 25mm Supersession > Use with item 19 & 20	2
37	826/01249	Nut Rivet M10	1
38	1420/0008Z	Washer Plain M10 Supersession >	1
39	1425/0008Z	Spring Washer M10 Supersession >	1
40	1315/0410Z	Setscrew M10 x 40 < Supersession	1
41	821/00213	Clamp top	1

42	821/00214	Clamp base	1
43	821/00215	Insert clamp	1
44	1406/0018	Washer Bonded (1/2" BSP) < Supersession	1