




1	25/220527	Valve solenoid change-over 6 ports 4 cartridge Supersession >	1
2	:25/983802	Coil 12v < Supersession	4
3	331/16696	Plate mounting change over valve	1
4	123/05836	Clamp < Supersession	2
4A	123/07146	Plate clamp stiffener	1
5	1315/3414Z	Bolt M10x60	4
6	1420/0008Z	Washer Plain M10 Supersession >	2
7	1370/0303Z	Nut Lock M10 Supersession >	2
8	123/02569	Clip 'S'	2
9	826/01249	Nut Rivet M10	2
10	816/13208	Adapter 90 deg elbow Supersession >	2
11	:2401/0507	O Ring	1
12	612/80054	Hose	1
13	612/80054	Hose	1
14	331/18864	Plate adapter 6 hose	1
15	612/37011	Hose 3/8in. HP	1
16	612/37011	Hose 3/8in. HP	1
17	816/20012	Adapter M/F	2
18	123/03286	Pipe left hand Supersession >	1
19	123/03285	Pipe Supersession >	1
20	1315/0410Z	Setscrew M10 x 40 < Supersession	4

21	1420/0008Z	Washer Plain M10 Supersession >	4
22	1356/0203Z	Nut Backing 3/8"BSP	2
23	613/27200	Hose 1/2"BSP x 1130mm	1
24	613/27200	Hose 1/2"BSP x 1130mm	1
25	658/10074	Pipe inner dipper left hand jaw	1
26	658/10073	Pipe inner dipper right hand jaw	1
27	826/01106	Nut Rivet M8 < Supersession	4
28	1420/0007Z	Washer (M8) Supersession >	4
29	1315/0308Z	Setscrew M8 x 30	4
30	1406/0018	Washer Bonded (1/2" BSP) < Supersession	2
31	45/910400	Coupling 1/2" BSP female quick release < Supersession	1
32	45/910500	Coupling 1/2" BSP male quick release < Supersession	1
33	⊘ Not for sale	'See Remark' Bucket ram see frame E1-10-13	1
34	⊘ Not for sale	'See Remark' Extention ram see E1-11-4	1
35	835/10082	Cap flip top protection < Supersession	1
36	980/67301	Cap Coupling to fit 1/2 male	1